



# TYPICAL BASELINE OHMIC VALUES (ON FLOAT)

BATTERY TYPE	BASELINE OHMIC VALUES ON FLOAT			
	MIDTRONICS** (SIEMEN'S)	ALBER CELLCORDER (MILLI-OHMS)	BIDDLE BITE 2 (MILLI-OHMS)	BIDDLE MBITE (MILLI-OHMS)
HT145ET	1663	3.975	3.215	3.484
HT170ET	1754	3.769	3.048	3.303
HT200ET	2268	2.914	2.357	2.554
HT7500ET	2499	2.644	2.139	2.318

- The above data are typical results and do not form a specification.
- Values are subject to change without notification.
- These values are not to be used to determine warranty claims.
- \*\* = Midtronics Meters include: Micro Celltron CTM-100  
Celltron Advance CTA-2000  
Celltron Ultra CTU-6000
- For batteries not listed contact East Penn Manufacturing.

Suspect ohmic values should be confirmed with a discharge test to determine the true capacity. Reference values stored in an ohmic meter must agree with the above tables for best results. Testers with pass/fail modes must use algorithms based on these reference values; although, a more thorough method of testing is recommended.

DISTRIBUTED BY:



**East Penn Manufacturing Co.**

Lyon Station, PA 19536-0147

Phone: 610-682-6361 Fax: 610-682-4781

[www.dekabatteries.com](http://www.dekabatteries.com)

E.P.M. Form No. 2312 1/17

© 2017 by EPM Printed in U.S.A.

All data subject to change without notice. No part of this document may be copied or reproduced, electronically or mechanically, without written permission from the company.